

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774778

Luminaire Tested: LD6D95BD010-EU6DR6570959040-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6570959040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7930.1 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774778
CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P774778

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	853075
5°	853778
10°	883842
15°	885306
20°	815073
25°	694474
30°	531653
35°	375606
40°	221704
45°	90007
50°	32619
55°	18173
60°	10423
65°	5739
70°	6038
75°	4686
80°	4908
85°	4137

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 90007 cd/sqm



TEST NUMBER: P774778

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	751.8	9.5
10°-20°	2168.7	27.3
20°-30°	2602.0	32.8
30°-40°	1748.6	22.1
40°-50°	523.4	6.6
50°-60°	92.4	1.2
60°-70°	26.3	0.3
70°-80°	12.9	0.2
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5522.4	69.6
0°-40°	7271.0	91.7
0°-60°	7886.8	99.5
0°-90°	7930.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7930.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7808	
5°	7784	752
15°	7827	2169
25°	5761	2602
35°	2816	1749
45°	582	523
55°	95	92
65°	22	26
75°	11	13
85°	3	4
90°	0	



TEST NUMBER: P774778

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	7807.7
2.5°	7841.0
5°	7784.4
7.5°	7902.0
10°	7966.4
12.5°	7950.8
15°	7826.6
17.5°	7522.6
20°	7010.0
22.5°	6406.4
25°	5760.6
27.5°	5031.7
30°	4214.0
32.5°	3472.8
35°	2816.0
37.5°	2166.9
40°	1554.4
42.5°	1015.2
45°	582.5
47.5°	308.4
50°	191.9
52.5°	133.1
55°	95.4
57.5°	68.8
60°	47.7
62.5°	31.1
65°	22.2
67.5°	20.0
70°	18.9
72.5°	14.4
75°	11.1
77.5°	10.0
80°	7.8
82.5°	5.5
85°	3.3
87.5°	2.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)