

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202613

Luminaire Tested: **LD6B15D010 EU6B10209040 6LBMWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202613  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B15D010 EU6B10209040 6LBMWMH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 998.2 lumens  
Efficiency: N/A  
Efficacy: 69.8 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202613

CATALOG NUMBER: LD6B15D010 EU6B10209040 6LBMWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202613

CATALOG NUMBER: LD6B15D010 EU6B10209040 6LBMWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74																			
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69																			
6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64																			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	62	60																			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56																			
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53																			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202613

CATALOG NUMBER: LD6B15D010 EU6B10209040 6LBMWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.9	10.2
10°-20°	261.6	26.2
20°-30°	321.3	32.2
30°-40°	220.3	22.1
40°-50°	70.8	7.1
50°-60°	14.4	1.4
60°-70°	5.6	0.6
70°-80°	2.1	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	684.7	68.6
0°-40°	905.0	90.7
0°-60°	990.2	99.2
0°-90°	998.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	998.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1110	
5°	1089	102
15°	936	262
25°	709	321
35°	351	220
45°	84	71
55°	14	14
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P202613

CATALOG NUMBER: LD6B15D010 EU6B10209040 6LBMWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1110.2
2.5°	1103.4
5°	1089.0
7.5°	1061.9
10°	1025.5
12.5°	980.6
15°	935.7
17.5°	885.8
20°	830.7
22.5°	773.1
25°	708.8
27.5°	637.6
30°	547.9
32.5°	448.8
35°	351.4
37.5°	262.5
40°	188.8
42.5°	128.7
45°	83.8
47.5°	51.7
50°	31.3
52.5°	19.5
55°	14.4
57.5°	11.0
60°	8.5
62.5°	6.8
65°	5.9
67.5°	4.2
70°	3.4
72.5°	2.5
75°	1.7
77.5°	1.7
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)