

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203541

Luminaire Tested: **LD6B15D010 EU6B10209050 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203541  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B15D010 EU6B10209050 6LBMMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1024.4 lumens  
Efficiency: N/A  
Efficacy: 71.6 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203541

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203541

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203541

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.6	6.9
10°-20°	189.1	18.5
20°-30°	253.9	24.8
30°-40°	208.3	20.3
40°-50°	125.1	12.2
50°-60°	83.1	8.1
60°-70°	55.7	5.4
70°-80°	30.0	2.9
80°-90°	8.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.7	50.1
0°-40°	722.0	70.5
0°-60°	930.2	90.8
0°-90°	1024.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1024.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	764	
5°	752	71
15°	674	189
25°	560	254
35°	331	208
45°	158	125
55°	92	83
65°	56	56
75°	28	30
85°	7	8
90°	0	



TEST NUMBER: P203541

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	764.3
2.5°	758.7
5°	751.6
7.5°	736.1
10°	717.7
12.5°	695.1
15°	673.9
17.5°	648.5
20°	623.1
22.5°	594.8
25°	559.5
27.5°	517.1
30°	460.6
32.5°	397.0
35°	330.6
37.5°	274.1
40°	226.1
42.5°	187.9
45°	158.2
47.5°	134.2
50°	117.3
52.5°	103.1
55°	91.8
57.5°	81.9
60°	73.5
62.5°	63.6
65°	56.5
67.5°	48.0
70°	41.0
72.5°	33.9
75°	28.3
77.5°	22.6
80°	17.0
82.5°	12.7
85°	7.1
87.5°	2.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)