

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774858

Luminaire Tested: LD6D95BD010-EU6DR7070959050-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR7070959050-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11825.4 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774858

CATALOG NUMBER: LD6D95BD010-EU6DR7070959050-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P774858

CATALOG NUMBER: LD6D95BD010-EU6DR7070959050-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 95 | 94 | 93 | 93 | 93 | 93 |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 92 | 97 | 93 | 90 | 94 | 91 | 88 | 91 | 89 | 87 | 85 | 85 | 85 | 85 |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 85 | 82 | 87 | 84 | 81 | 85 | 82 | 79 | 78 | 78 | 78 | 78 |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 83 | 78 | 75 | 81 | 77 | 74 | 79 | 76 | 73 | 71 | 71 | 71 | 71 |
| 5 | 89 | 80 | 74 | 69 | 88 | 79 | 73 | 69 | 78 | 72 | 68 | 76 | 71 | 68 | 74 | 70 | 67 | 65 | 65 | 65 | 65 |
| 6 | 84 | 75 | 68 | 63 | 83 | 74 | 68 | 63 | 72 | 67 | 63 | 71 | 66 | 62 | 69 | 65 | 62 | 60 | 60 | 60 | 60 |
| 7 | 80 | 69 | 63 | 58 | 78 | 69 | 62 | 58 | 67 | 62 | 58 | 66 | 61 | 57 | 65 | 61 | 57 | 56 | 56 | 56 | 56 |
| 8 | 75 | 65 | 58 | 54 | 74 | 64 | 58 | 54 | 63 | 57 | 53 | 62 | 57 | 53 | 61 | 56 | 53 | 51 | 51 | 51 | 51 |
| 9 | 71 | 61 | 54 | 50 | 70 | 60 | 54 | 50 | 59 | 53 | 50 | 58 | 53 | 49 | 57 | 53 | 49 | 48 | 48 | 48 | 48 |
| 10 | 67 | 57 | 50 | 46 | 66 | 56 | 50 | 46 | 55 | 50 | 46 | 55 | 50 | 46 | 54 | 49 | 46 | 44 | 44 | 44 | 44 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1019796 |
| 5° | 1017254 |
| 10° | 1015047 |
| 15° | 1014766 |
| 20° | 1004842 |
| 25° | 943929 |
| 30° | 841510 |
| 35° | 670942 |
| 40° | 445504 |
| 45° | 266343 |
| 50° | 138091 |
| 55° | 72577 |
| 60° | 25676 |
| 65° | 440 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 266343 cd/sqm



TEST NUMBER: P774858

CATALOG NUMBER: LD6D95BD010-EU6DR7070959050-6LBCSSQMB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 882.0 | 7.5 |
| 10°-20° | 2529.7 | 21.4 |
| 20°-30° | 3568.7 | 30.2 |
| 30°-40° | 3080.7 | 26.1 |
| 40°-50° | 1379.6 | 11.7 |
| 50°-60° | 361.2 | 3.1 |
| 60°-70° | 23.5 | 0.2 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 6980.4 | 59.0 |
| 0°-40° | 10061.1 | 85.1 |
| 0°-60° | 11801.9 | 99.8 |
| 0°-90° | 11825.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 11825.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 9334 | |
| 5° | 9275 | 882 |
| 15° | 8971 | 2530 |
| 25° | 7830 | 3569 |
| 35° | 5030 | 3081 |
| 45° | 1724 | 1380 |
| 55° | 381 | 361 |
| 65° | 2 | 24 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P774858

CATALOG NUMBER: LD6D95BD010-EU6DR7070959050-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 9333.6 |
| 2.5° | 9323.6 |
| 5° | 9274.9 |
| 7.5° | 9234.6 |
| 10° | 9149.0 |
| 12.5° | 9071.8 |
| 15° | 8971.1 |
| 17.5° | 8855.3 |
| 20° | 8642.1 |
| 22.5° | 8291.3 |
| 25° | 7829.8 |
| 27.5° | 7294.4 |
| 30° | 6670.0 |
| 32.5° | 5906.3 |
| 35° | 5030.2 |
| 37.5° | 4063.4 |
| 40° | 3123.5 |
| 42.5° | 2373.3 |
| 45° | 1723.7 |
| 47.5° | 1188.3 |
| 50° | 812.4 |
| 52.5° | 560.6 |
| 55° | 381.0 |
| 57.5° | 229.9 |
| 60° | 117.5 |
| 62.5° | 36.9 |
| 65° | 1.7 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)