

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202614

Luminaire Tested: **LD6B15D010 EU6B10209050 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10209050 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1002.2 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202614

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202614

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74		
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69		
6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64		
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60		
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56		
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53		
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202614

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	10.2
10°-20°	262.6	26.2
20°-30°	322.5	32.2
30°-40°	221.1	22.1
40°-50°	71.1	7.1
50°-60°	14.4	1.4
60°-70°	5.7	0.6
70°-80°	2.1	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.3	68.6
0°-40°	908.5	90.6
0°-60°	994.0	99.2
0°-90°	1002.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1002.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1114	
5°	1093	102
15°	939	263
25°	712	323
35°	353	221
45°	84	71
55°	14	14
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P202614

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1114.4
2.5°	1107.6
5°	1093.1
7.5°	1065.9
10°	1029.4
12.5°	984.3
15°	939.3
17.5°	889.1
20°	833.9
22.5°	776.1
25°	711.5
27.5°	640.1
30°	550.0
32.5°	450.5
35°	352.8
37.5°	263.5
40°	189.6
42.5°	129.2
45°	84.2
47.5°	51.9
50°	31.5
52.5°	19.6
55°	14.5
57.5°	11.1
60°	8.5
62.5°	6.8
65°	6.0
67.5°	4.3
70°	3.4
72.5°	2.6
75°	1.7
77.5°	1.7
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)