

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774869

Luminaire Tested: LD6D95BD010-EU6DR7070959050-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR7070959050-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7426.7 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774869
CATALOG NUMBER: LD6D95BD010-EU6DR7070959050-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P774869

CATALOG NUMBER: LD6D95BD010-EU6DR7070959050-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	912295
5°	885179
10°	860510
15°	849223
20°	792993
25°	595739
30°	421134
35°	149175
40°	78432
45°	83548
50°	86520
55°	88140
60°	88676
65°	86815
70°	81941
75°	75903
80°	67388
85°	54658

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 88722 cd/sqm



TEST NUMBER: P774869

CATALOG NUMBER: LD6D95BD010-EU6DR7070959050-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	761.2	10.3
10°-20°	2088.1	28.1
20°-30°	2299.7	31.0
30°-40°	878.6	11.8
40°-50°	414.9	5.6
50°-60°	412.5	5.6
60°-70°	330.2	4.4
70°-80°	189.8	2.6
80°-90°	51.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5149.0	69.3
0°-40°	6027.7	81.2
0°-60°	6855.0	92.3
0°-90°	7426.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7426.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8350	
5°	8071	761
15°	7508	2088
25°	4942	2300
35°	1118	879
45°	541	415
55°	463	412
65°	336	330
75°	180	190
85°	44	52
90°	0	



TEST NUMBER: P774869

CATALOG NUMBER: LD6D95BD010-EU6DR7070959050-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8349.7
2.5°	8262.4
5°	8070.7
7.5°	7910.8
10°	7756.1
12.5°	7625.2
15°	7507.6
17.5°	7223.3
20°	6820.1
22.5°	5950.3
25°	4941.6
27.5°	4301.7
30°	3338.0
32.5°	2156.2
35°	1118.4
37.5°	604.1
40°	549.9
42.5°	546.0
45°	540.7
47.5°	528.8
50°	509.0
52.5°	486.5
55°	462.7
57.5°	436.3
60°	405.8
62.5°	371.5
65°	335.8
67.5°	296.1
70°	256.5
72.5°	216.8
75°	179.8
77.5°	141.5
80°	107.1
82.5°	75.4
85°	43.6
87.5°	17.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)