

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204262

Luminaire Tested: **LD6B15D010 EU6B10209050 6LBSWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204262  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B15D010 EU6B10209050 6LBSWH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1337.5 lumens  
Efficiency: N/A  
Efficacy: 93.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204262

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBSWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204262

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBSWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89					89			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204262

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBSWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.6	5.5
10°-20°	190.4	14.2
20°-30°	249.1	18.6
30°-40°	263.7	19.7
40°-50°	246.0	18.4
50°-60°	186.3	13.9
60°-70°	100.9	7.5
70°-80°	27.0	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.1	38.4
0°-40°	776.8	58.1
0°-60°	1209.1	90.4
0°-90°	1337.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1337.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	798	
5°	786	74
15°	681	190
25°	542	249
35°	422	264
45°	320	246
55°	209	186
65°	101	101
75°	23	27
85°	0	0
90°	0	



TEST NUMBER: P204262

CATALOG NUMBER: LD6B15D010 EU6B10209050 6LBSWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	797.7
2.5°	794.8
5°	786.0
7.5°	767.0
10°	742.1
12.5°	712.8
15°	680.6
17.5°	644.0
20°	611.8
22.5°	575.2
25°	541.6
27.5°	507.9
30°	475.7
32.5°	447.9
35°	421.5
37.5°	395.2
40°	370.3
42.5°	345.4
45°	320.5
47.5°	292.7
50°	264.9
52.5°	237.1
55°	209.3
57.5°	180.0
60°	152.2
62.5°	125.9
65°	101.0
67.5°	77.6
70°	57.1
72.5°	39.5
75°	23.4
77.5°	10.2
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)