

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205476

Luminaire Tested: **LD6B10D010 EU6B10209024 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205476
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209024 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 428.4 lumens
Efficiency: N/A
Efficacy: 43.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205476

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205476

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																											
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																											
3	102	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79																											
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73																											
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																											
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																											
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																											
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																											
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																											
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																											

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205476

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.0	9.6
10°-20°	106.4	24.8
20°-30°	135.6	31.6
30°-40°	95.8	22.4
40°-50°	35.0	8.2
50°-60°	9.7	2.3
60°-70°	3.5	0.8
70°-80°	1.3	0.3
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	283.0	66.1
0°-40°	378.8	88.4
0°-60°	423.5	98.9
0°-90°	428.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	428.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	446	
5°	439	41
15°	379	106
25°	301	136
35°	152	96
45°	42	35
55°	10	10
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P205476

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	446.4
2.5°	444.7
5°	438.6
7.5°	426.5
10°	413.5
12.5°	396.2
15°	378.9
17.5°	361.6
20°	344.3
22.5°	323.6
25°	301.1
27.5°	269.9
30°	235.3
32.5°	193.8
35°	152.3
37.5°	115.9
40°	84.8
42.5°	61.4
45°	42.4
47.5°	28.5
50°	19.0
52.5°	13.0
55°	10.4
57.5°	7.8
60°	6.1
62.5°	4.3
65°	3.5
67.5°	2.6
70°	1.7
72.5°	1.7
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)