

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203627

Luminaire Tested: **LD6B10D010 EU6B10209024 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203627
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209024 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 483.0 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203627

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203627

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203627

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	11.5
10°-20°	132.8	27.5
20°-30°	152.1	31.5
30°-40°	102.2	21.2
40°-50°	29.2	6.0
50°-60°	7.1	1.5
60°-70°	2.7	0.6
70°-80°	1.1	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.5	70.5
0°-40°	442.7	91.7
0°-60°	479.1	99.2
0°-90°	483.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	483.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	619	
5°	602	56
15°	476	133
25°	332	152
35°	163	102
45°	34	29
55°	8	7
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P203627

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	619.1
2.5°	614.7
5°	601.5
7.5°	577.7
10°	548.6
12.5°	511.6
15°	476.4
17.5°	439.4
20°	402.4
22.5°	367.2
25°	332.0
27.5°	299.4
30°	261.5
32.5°	211.4
35°	162.9
37.5°	118.9
40°	81.9
42.5°	53.7
45°	33.5
47.5°	20.3
50°	12.3
52.5°	9.7
55°	7.9
57.5°	6.2
60°	4.4
62.5°	3.5
65°	2.6
67.5°	1.8
70°	1.8
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)