

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203545

Luminaire Tested: **LD6B20D010 EU6B10208030 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208030 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1634.5 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203545

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203545

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203545

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	6.9
10°-20°	301.8	18.5
20°-30°	405.2	24.8
30°-40°	332.4	20.3
40°-50°	199.6	12.2
50°-60°	132.6	8.1
60°-70°	88.9	5.4
70°-80°	47.9	2.9
80°-90°	13.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	819.6	50.1
0°-40°	1152.0	70.5
0°-60°	1484.3	90.8
0°-90°	1634.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1634.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1220	
5°	1199	113
15°	1075	302
25°	893	405
35°	528	332
45°	252	200
55°	146	133
65°	90	89
75°	45	48
85°	11	14
90°	0	



TEST NUMBER: P203545

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1219.6
2.5°	1210.6
5°	1199.3
7.5°	1174.5
10°	1145.2
12.5°	1109.1
15°	1075.3
17.5°	1034.7
20°	994.2
22.5°	949.1
25°	892.7
27.5°	825.1
30°	734.9
32.5°	633.5
35°	527.5
37.5°	437.3
40°	360.7
42.5°	299.8
45°	252.5
47.5°	214.2
50°	187.1
52.5°	164.6
55°	146.5
57.5°	130.8
60°	117.2
62.5°	101.4
65°	90.2
67.5°	76.6
70°	65.4
72.5°	54.1
75°	45.1
77.5°	36.1
80°	27.1
82.5°	20.3
85°	11.3
87.5°	4.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)