

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203009

Luminaire Tested: **LD6B10D010 EU6B10209024 6LBWB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203009  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B10D010 EU6B10209024 6LBWB1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 431.9 lumens  
Efficiency: N/A  
Efficacy: 43.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203009

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBWB1

### Luminous Intensity Polar Plot





TEST NUMBER: P203009

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBWB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77																
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70																
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64																
6	83	73	67	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59			59																
7	78	68	61	56	77	67	61	56	66	60	56	65	60	56	63	59	55	54			54																
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50																
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46			46																
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	42			42																

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203009

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBWB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	30.6	7.1
10°-20°	85.6	19.8
20°-30°	119.9	27.8
30°-40°	114.5	26.5
40°-50°	65.2	15.1
50°-60°	15.9	3.7
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	236.1	54.7
0°-40°	350.6	81.2
0°-60°	431.7	99.9
0°-90°	431.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	431.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	326	
5°	323	31
15°	304	86
25°	262	120
35°	186	114
45°	84	65
55°	16	16
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203009

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBWB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	325.5
2.5°	325.5
5°	322.9
7.5°	319.4
10°	316.7
12.5°	311.4
15°	303.5
17.5°	296.5
20°	287.7
22.5°	276.3
25°	262.2
27.5°	246.3
30°	228.7
32.5°	207.6
35°	186.5
37.5°	161.0
40°	133.7
42.5°	108.2
45°	83.6
47.5°	61.6
50°	43.1
52.5°	27.3
55°	15.8
57.5°	7.0
60°	1.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)