

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204576

Luminaire Tested: **LD6B20D010 EU6B10208030 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208030 6LB5MW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2287.4 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204576

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204576

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204576

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.3	3.8
10°-20°	248.9	10.9
20°-30°	374.9	16.4
30°-40°	446.0	19.5
40°-50°	445.2	19.5
50°-60°	362.1	15.8
60°-70°	222.8	9.7
70°-80°	86.3	3.8
80°-90°	13.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.1	31.1
0°-40°	1157.1	50.6
0°-60°	1964.5	85.9
0°-90°	2287.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2287.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	922	
5°	919	87
15°	884	249
25°	816	375
35°	714	446
45°	579	445
55°	405	362
65°	224	223
75°	79	86
85°	11	14
90°	0	



TEST NUMBER: P204576

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	921.6
2.5°	922.9
5°	918.9
7.5°	913.4
10°	906.7
12.5°	894.5
15°	883.6
17.5°	867.4
20°	849.7
22.5°	833.5
25°	815.9
27.5°	791.5
30°	767.1
32.5°	744.0
35°	714.2
37.5°	681.7
40°	651.9
42.5°	615.3
45°	578.7
47.5°	539.4
50°	497.4
52.5°	454.0
55°	405.2
57.5°	357.8
60°	311.7
62.5°	267.0
65°	223.6
67.5°	183.0
70°	145.0
72.5°	109.8
75°	78.6
77.5°	51.5
80°	31.2
82.5°	19.0
85°	10.8
87.5°	5.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)