

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205368

Luminaire Tested: **LD6B10D010 EU6B10208027 6LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205368  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B10D010 EU6B10208027 6LBSLI1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1096.3 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205368

CATALOG NUMBER: LD6B10D010 EU6B10208027 6LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205368

CATALOG NUMBER: LD6B10D010 EU6B10208027 6LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205368

CATALOG NUMBER: LD6B10D010 EU6B10208027 6LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.7	5.8
10°-20°	162.3	14.8
20°-30°	206.9	18.9
30°-40°	214.6	19.6
40°-50°	197.8	18.0
50°-60°	148.7	13.6
60°-70°	80.3	7.3
70°-80°	21.5	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	433.0	39.5
0°-40°	647.6	59.1
0°-60°	994.1	90.7
0°-90°	1096.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1096.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	692	
5°	681	64
15°	579	162
25°	450	207
35°	342	215
45°	257	198
55°	166	149
65°	80	80
75°	19	22
85°	0	0
90°	0	



TEST NUMBER: P205368

CATALOG NUMBER: LD6B10D010 EU6B10208027 6LBSL11

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	691.8
2.5°	689.5
5°	681.3
7.5°	666.2
10°	639.4
12.5°	612.6
15°	578.8
17.5°	547.4
20°	514.8
22.5°	481.0
25°	449.5
27.5°	419.3
30°	391.3
32.5°	365.7
35°	342.4
37.5°	320.3
40°	299.3
42.5°	277.2
45°	257.4
47.5°	235.3
50°	213.1
52.5°	189.8
55°	166.5
57.5°	143.3
60°	121.1
62.5°	100.2
65°	80.4
67.5°	61.7
70°	45.4
72.5°	31.4
75°	18.6
77.5°	8.2
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)