

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35132

Luminaire Tested: **LD6B10D010 EU6B10209027 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35132
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209027 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 438.5 lumens
Efficiency: N/A
Efficacy: 45.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35132

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P35132

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76	76	76	76
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	79	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34773
5°	33924
10°	31732
15°	28773
20°	25688
25°	22675
30°	19135
35°	12504
40°	6302
45°	2307
50°	710
55°	455
60°	261
65°	154
70°	191
75°	0
80°	0
85°	0



TEST NUMBER: P35132

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	11.0
10°-20°	119.0	27.1
20°-30°	144.2	32.9
30°-40°	98.3	22.4
40°-50°	23.4	5.3
50°-60°	3.7	0.8
60°-70°	1.4	0.3
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	311.4	71.0
0°-40°	409.7	93.4
0°-60°	436.7	99.6
0°-90°	438.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	438.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	533	
5°	518	48
15°	426	119
25°	315	144
35°	157	98
45°	25	23
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P35132

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	533
2.5°	530
5°	518
7.5°	502
10°	479
12.5°	453
15°	426
17.5°	398
20°	370
22.5°	342
25°	315
27.5°	290
30°	254
32.5°	207
35°	157
37.5°	112
40°	74
42.5°	46
45°	25
47.5°	13
50°	7
52.5°	5
55°	4
57.5°	3
60°	2
62.5°	2
65°	1
67.5°	1
70°	1
72.5°	1
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)