

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202603

Luminaire Tested: **LD6B10D010 EU6B10209727 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209727 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 595.5 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202603

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202603

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74																			
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69																			
6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64																			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	62	60																			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56																			
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53																			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202603

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.8	10.2
10°-20°	156.0	26.2
20°-30°	191.6	32.2
30°-40°	131.4	22.1
40°-50°	42.2	7.1
50°-60°	8.6	1.4
60°-70°	3.3	0.6
70°-80°	1.3	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.4	68.6
0°-40°	539.8	90.7
0°-60°	590.7	99.2
0°-90°	595.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	595.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	662	
5°	650	61
15°	558	156
25°	423	192
35°	210	131
45°	50	42
55°	9	9
65°	4	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P202603

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	662.2
2.5°	658.2
5°	649.6
7.5°	633.4
10°	611.7
12.5°	584.9
15°	558.2
17.5°	528.4
20°	495.5
22.5°	461.2
25°	422.8
27.5°	380.4
30°	326.8
32.5°	267.7
35°	209.6
37.5°	156.6
40°	112.6
42.5°	76.8
45°	50.0
47.5°	30.8
50°	18.7
52.5°	11.6
55°	8.6
57.5°	6.6
60°	5.1
62.5°	4.0
65°	3.5
67.5°	2.5
70°	2.0
72.5°	1.5
75°	1.0
77.5°	1.0
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)