

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204447

Luminaire Tested: **LD6B10D010 EU6B10208030 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10208030 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 973.0 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204447

CATALOG NUMBER: LD6B10D010 EU6B10208030 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204447

CATALOG NUMBER: LD6B10D010 EU6B10208030 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88				88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76				76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	69	75	71	67	65				65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57				57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39				39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35				35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204447

CATALOG NUMBER: LD6B10D010 EU6B10208030 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.5	4.2
10°-20°	115.0	11.8
20°-30°	171.0	17.6
30°-40°	199.0	20.4
40°-50°	194.0	19.9
50°-60°	149.2	15.3
60°-70°	82.4	8.5
70°-80°	21.8	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.5	33.6
0°-40°	525.5	54.0
0°-60°	868.6	89.3
0°-90°	973.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	973.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	429	
5°	427	41
15°	407	115
25°	371	171
35°	320	199
45°	252	194
55°	166	149
65°	83	82
75°	18	22
85°	0	0
90°	0	



TEST NUMBER: P204447

CATALOG NUMBER: LD6B10D010 EU6B10208030 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	429.3
2.5°	429.3
5°	426.8
7.5°	423.1
10°	420.6
12.5°	413.2
15°	407.1
17.5°	400.9
20°	392.3
22.5°	383.6
25°	371.3
27.5°	358.9
30°	346.6
32.5°	333.0
35°	319.5
37.5°	302.2
40°	287.4
42.5°	271.4
45°	251.6
47.5°	233.1
50°	212.2
52.5°	190.0
55°	166.5
57.5°	144.3
60°	123.3
62.5°	102.4
65°	82.6
67.5°	64.1
70°	46.9
72.5°	32.1
75°	18.5
77.5°	8.6
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)