

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203556

Luminaire Tested: **LD6B20D010 EU6B10209730 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209730 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1220.1 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203556

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203556

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203556

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.1	6.9
10°-20°	225.3	18.5
20°-30°	302.5	24.8
30°-40°	248.1	20.3
40°-50°	149.0	12.2
50°-60°	99.0	8.1
60°-70°	66.4	5.4
70°-80°	35.7	2.9
80°-90°	10.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	611.8	50.1
0°-40°	860.0	70.5
0°-60°	1108.0	90.8
0°-90°	1220.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1220.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	910	
5°	895	84
15°	803	225
25°	666	302
35°	394	248
45°	188	149
55°	109	99
65°	67	66
75°	34	36
85°	8	10
90°	0	



TEST NUMBER: P203556

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	910.4
2.5°	903.7
5°	895.2
7.5°	876.7
10°	854.9
12.5°	827.9
15°	802.7
17.5°	772.4
20°	742.1
22.5°	708.5
25°	666.4
27.5°	615.9
30°	548.6
32.5°	472.9
35°	393.8
37.5°	326.5
40°	269.2
42.5°	223.8
45°	188.5
47.5°	159.9
50°	139.7
52.5°	122.8
55°	109.4
57.5°	97.6
60°	87.5
62.5°	75.7
65°	67.3
67.5°	57.2
70°	48.8
72.5°	40.4
75°	33.7
77.5°	26.9
80°	20.2
82.5°	15.1
85°	8.4
87.5°	3.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)