

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204071

Luminaire Tested: **LD6B20D010 EU6B10209730 6LBNMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204071  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B20D010 EU6B10209730 6LBNMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1098.1 lumens  
Efficiency: N/A  
Efficacy: 52.8 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204071

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBNMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204071

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBNMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90		
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204071

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBNMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.6	7.6
10°-20°	221.7	20.2
20°-30°	295.9	26.9
30°-40°	238.8	21.7
40°-50°	114.4	10.4
50°-60°	67.8	6.2
60°-70°	45.1	4.1
70°-80°	24.2	2.2
80°-90°	6.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.2	54.7
0°-40°	840.0	76.5
0°-60°	1022.2	93.1
0°-90°	1098.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1098.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	900	
5°	890	84
15°	789	222
25°	648	296
35°	382	239
45°	141	114
55°	75	68
65°	45	45
75°	23	24
85°	5	7
90°	0	



TEST NUMBER: P204071

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBNMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	900.5
2.5°	900.5
5°	890.1
7.5°	872.6
10°	848.2
12.5°	822.0
15°	788.9
17.5°	757.4
20°	722.5
22.5°	685.9
25°	647.5
27.5°	607.3
30°	549.8
32.5°	469.5
35°	382.2
37.5°	301.9
40°	233.9
42.5°	181.5
45°	141.4
47.5°	111.7
50°	94.2
52.5°	83.8
55°	75.0
57.5°	68.1
60°	59.3
62.5°	52.4
65°	45.4
67.5°	38.4
70°	33.2
72.5°	27.9
75°	22.7
77.5°	17.5
80°	14.0
82.5°	10.5
85°	5.2
87.5°	1.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)