

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202835

Luminaire Tested: **LD6B20D010 EU6B10209730 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202835
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209730 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1390.9 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202835

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202835

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68		
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62		
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202835

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	6.0
10°-20°	246.9	17.8
20°-30°	371.7	26.7
30°-40°	380.1	27.3
40°-50°	230.8	16.6
50°-60°	65.0	4.7
60°-70°	9.9	0.7
70°-80°	3.2	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.7	50.4
0°-40°	1081.8	77.8
0°-60°	1377.6	99.0
0°-90°	1390.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1390.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	864	
5°	867	83
15°	874	247
25°	812	372
35°	616	380
45°	297	231
55°	65	65
65°	9	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P202835

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	863.9
2.5°	863.9
5°	867.4
7.5°	872.6
10°	872.6
12.5°	876.1
15°	874.4
17.5°	870.9
20°	858.7
22.5°	841.2
25°	811.5
27.5°	778.4
30°	733.0
32.5°	678.9
35°	616.1
37.5°	546.3
40°	466.0
42.5°	382.2
45°	296.7
47.5°	219.9
50°	155.3
52.5°	104.7
55°	64.6
57.5°	38.4
60°	19.2
62.5°	12.2
65°	8.7
67.5°	7.0
70°	5.2
72.5°	3.5
75°	3.5
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)