

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203649

Luminaire Tested: **LD6B20D010 EU6B10208035 6LBNH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203649  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B20D010 EU6B10208035 6LBNH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1313.7 lumens  
Efficiency: N/A  
Efficacy: 63.2 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203649

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBNH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203649

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBNH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54																			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203649

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBNH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.4	11.5
10°-20°	361.1	27.5
20°-30°	413.7	31.5
30°-40°	278.0	21.2
40°-50°	79.4	6.0
50°-60°	19.4	1.5
60°-70°	7.4	0.6
70°-80°	2.9	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	926.3	70.5
0°-40°	1204.3	91.7
0°-60°	1303.1	99.2
0°-90°	1313.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1313.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1684	
5°	1636	151
15°	1296	361
25°	903	414
35°	443	278
45°	91	79
55°	22	19
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P203649

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBNH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1684.0
2.5°	1672.0
5°	1636.1
7.5°	1571.4
10°	1492.3
12.5°	1391.7
15°	1295.9
17.5°	1195.3
20°	1094.7
22.5°	998.9
25°	903.1
27.5°	814.4
30°	711.4
32.5°	574.9
35°	443.2
37.5°	323.4
40°	222.8
42.5°	146.1
45°	91.0
47.5°	55.1
50°	33.5
52.5°	26.3
55°	21.6
57.5°	16.8
60°	12.0
62.5°	9.6
65°	7.2
67.5°	4.8
70°	4.8
72.5°	2.4
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)