

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203530

Luminaire Tested: **LD6B10D010 EU6B10209730 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203530
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209730 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 636.2 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203530

CATALOG NUMBER: LD6B10D010 EU6B10209730 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203530

CATALOG NUMBER: LD6B10D010 EU6B10209730 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203530

CATALOG NUMBER: LD6B10D010 EU6B10209730 6LBMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.9	6.9
10°-20°	117.5	18.5
20°-30°	157.7	24.8
30°-40°	129.4	20.3
40°-50°	77.7	12.2
50°-60°	51.6	8.1
60°-70°	34.6	5.4
70°-80°	18.6	2.9
80°-90°	5.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	319.0	50.1
0°-40°	448.4	70.5
0°-60°	577.7	90.8
0°-90°	636.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	636.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	475	
5°	467	44
15°	418	117
25°	348	158
35°	205	129
45°	98	78
55°	57	52
65°	35	35
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P203530

CATALOG NUMBER: LD6B10D010 EU6B10209730 6LBMMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	474.7
2.5°	471.2
5°	466.8
7.5°	457.2
10°	445.7
12.5°	431.7
15°	418.5
17.5°	402.7
20°	387.0
22.5°	369.4
25°	347.5
27.5°	321.1
30°	286.0
32.5°	246.6
35°	205.3
37.5°	170.2
40°	140.4
42.5°	116.7
45°	98.3
47.5°	83.4
50°	72.8
52.5°	64.1
55°	57.0
57.5°	50.9
60°	45.6
62.5°	39.5
65°	35.1
67.5°	29.8
70°	25.4
72.5°	21.1
75°	17.5
77.5°	14.0
80°	10.5
82.5°	7.9
85°	4.4
87.5°	1.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)