

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204370

Luminaire Tested: **LD6B20D010 EU6B10208035 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208035 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1995.6 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204370

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204370

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204370

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.3	4.4
10°-20°	245.0	12.3
20°-30°	357.3	17.9
30°-40°	407.4	20.4
40°-50°	390.8	19.6
50°-60°	299.3	15.0
60°-70°	164.3	8.2
70°-80°	43.7	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	689.5	34.5
0°-40°	1096.9	55.0
0°-60°	1787.0	89.5
0°-90°	1995.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1995.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	927	
5°	920	87
15°	869	245
25°	776	357
35°	651	407
45°	508	391
55°	335	299
65°	165	164
75°	38	44
85°	0	1
90°	0	



TEST NUMBER: P204370

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	926.9
2.5°	924.5
5°	919.7
7.5°	912.5
10°	902.9
12.5°	886.1
15°	869.4
17.5°	850.2
20°	828.7
22.5°	802.3
25°	776.0
27.5°	749.6
30°	716.1
32.5°	685.0
35°	651.4
37.5°	617.9
40°	584.4
42.5°	548.5
45°	507.7
47.5°	467.0
50°	423.9
52.5°	378.4
55°	335.3
57.5°	292.2
60°	246.7
62.5°	203.6
65°	165.3
67.5°	126.9
70°	93.4
72.5°	62.3
75°	38.3
77.5°	16.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)