

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204790

Luminaire Tested: **LD6B20D010 EU6B10209035 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209035 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1939.3 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204790

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204790

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204790

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.0	3.9
10°-20°	213.7	11.0
20°-30°	321.4	16.6
30°-40°	380.9	19.6
40°-50°	379.0	19.5
50°-60°	305.6	15.8
60°-70°	184.9	9.5
70°-80°	68.6	3.5
80°-90°	10.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.1	31.5
0°-40°	991.0	51.1
0°-60°	1675.6	86.4
0°-90°	1939.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1939.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	792	
5°	789	75
15°	757	214
25°	698	321
35°	610	381
45°	494	379
55°	341	306
65°	186	185
75°	62	69
85°	8	10
90°	0	



TEST NUMBER: P204790

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	792.1
2.5°	792.1
5°	788.6
7.5°	786.2
10°	779.2
12.5°	767.4
15°	756.8
17.5°	745.1
20°	731.0
22.5°	716.9
25°	698.1
27.5°	678.1
30°	655.8
32.5°	634.6
35°	609.9
37.5°	584.1
40°	553.5
42.5°	524.1
45°	493.6
47.5°	459.5
50°	421.9
52.5°	383.1
55°	340.8
57.5°	303.2
60°	260.9
62.5°	223.3
65°	185.7
67.5°	150.4
70°	117.5
72.5°	88.1
75°	62.3
77.5°	40.0
80°	23.5
82.5°	14.1
85°	8.2
87.5°	3.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)