

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202702

Luminaire Tested: **LD6B10D010 EU6B10209035 6LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202702  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B10D010 EU6B10209035 6LBWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 815.0 lumens  
Efficiency: N/A  
Efficacy: 82.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202702

CATALOG NUMBER: LD6B10D010 EU6B10209035 6LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202702

CATALOG NUMBER: LD6B10D010 EU6B10209035 6LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202702

CATALOG NUMBER: LD6B10D010 EU6B10209035 6LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.5	5.8
10°-20°	134.7	16.5
20°-30°	197.5	24.2
30°-40°	205.6	25.2
40°-50°	142.2	17.5
50°-60°	61.9	7.6
60°-70°	19.0	2.3
70°-80°	5.7	0.7
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.7	46.6
0°-40°	585.3	71.8
0°-60°	789.4	96.9
0°-90°	815.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	815.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	503	
5°	500	47
15°	478	135
25°	432	198
35°	333	206
45°	184	142
55°	66	62
65°	18	19
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P202702

CATALOG NUMBER: LD6B10D010 EU6B10209035 6LBWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	502.6
2.5°	503.7
5°	500.5
7.5°	496.3
10°	491.0
12.5°	485.7
15°	478.4
17.5°	468.9
20°	458.3
22.5°	446.7
25°	431.9
27.5°	412.9
30°	388.6
32.5°	363.3
35°	332.6
37.5°	298.8
40°	259.8
42.5°	220.7
45°	183.7
47.5°	148.9
50°	118.3
52.5°	89.8
55°	66.5
57.5°	47.5
60°	32.7
62.5°	24.3
65°	18.0
67.5°	13.7
70°	9.5
72.5°	7.4
75°	5.3
77.5°	3.2
80°	2.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)