

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204067

Luminaire Tested: **LD6B20D010 EU6B10209035 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209035 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1274.5 lumens
Efficiency: N/A
Efficacy: 61.3 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204067

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204067

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90																												
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81																												
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73																												
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66																												
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61																												
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56																												
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																												
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47																												
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44																												
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204067

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.1	7.6
10°-20°	257.3	20.2
20°-30°	343.5	26.9
30°-40°	277.1	21.7
40°-50°	132.8	10.4
50°-60°	78.7	6.2
60°-70°	52.4	4.1
70°-80°	28.0	2.2
80°-90°	7.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	697.8	54.7
0°-40°	974.8	76.5
0°-60°	1186.4	93.1
0°-90°	1274.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1274.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1045	
5°	1033	97
15°	916	257
25°	752	343
35°	444	277
45°	164	133
55°	87	79
65°	53	52
75°	26	28
85°	6	8
90°	0	



TEST NUMBER: P204067

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1045.2
2.5°	1045.2
5°	1033.0
7.5°	1012.8
10°	984.4
12.5°	954.0
15°	915.5
17.5°	879.1
20°	838.6
22.5°	796.0
25°	751.5
27.5°	704.9
30°	638.0
32.5°	544.9
35°	443.6
37.5°	350.4
40°	271.4
42.5°	210.7
45°	164.1
47.5°	129.6
50°	109.4
52.5°	97.2
55°	87.1
57.5°	79.0
60°	68.9
62.5°	60.8
65°	52.7
67.5°	44.6
70°	38.5
72.5°	32.4
75°	26.3
77.5°	20.3
80°	16.2
82.5°	12.2
85°	6.1
87.5°	2.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)