

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204170

Luminaire Tested: **LD6B20D010 EU6B10209035 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209035 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1838.8 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204170
CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204170

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204170

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.1	4.9
10°-20°	244.8	13.3
20°-30°	340.0	18.5
30°-40°	371.1	20.2
40°-50°	346.1	18.8
50°-60°	262.7	14.3
60°-70°	143.9	7.8
70°-80°	39.6	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	674.9	36.7
0°-40°	1046.0	56.9
0°-60°	1654.9	90.0
0°-90°	1838.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1838.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	962	
5°	954	90
15°	873	245
25°	739	340
35°	593	371
45°	450	346
55°	294	263
65°	144	144
75°	34	40
85°	0	1
90°	0	



TEST NUMBER: P204170

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	961.7
2.5°	961.7
5°	953.6
7.5°	941.5
10°	923.2
12.5°	898.9
15°	872.6
17.5°	840.2
20°	809.9
22.5°	773.4
25°	739.0
27.5°	704.6
30°	666.1
32.5°	629.7
35°	593.2
37.5°	556.8
40°	522.4
42.5°	485.9
45°	449.5
47.5°	413.0
50°	372.5
52.5°	334.1
55°	293.6
57.5°	255.1
60°	216.6
62.5°	178.2
65°	143.8
67.5°	111.4
70°	83.0
72.5°	56.7
75°	34.4
77.5°	16.2
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)