

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204689

Luminaire Tested: **LD6B20D010 EU6B10209050 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204689
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209050 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1993.3 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204689

CATALOG NUMBER: LD6B20D010 EU6B10209050 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204689

CATALOG NUMBER: LD6B20D010 EU6B10209050 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204689

CATALOG NUMBER: LD6B20D010 EU6B10209050 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.1	3.8
10°-20°	216.9	10.9
20°-30°	326.7	16.4
30°-40°	388.7	19.5
40°-50°	388.0	19.5
50°-60°	315.5	15.8
60°-70°	194.1	9.7
70°-80°	75.2	3.8
80°-90°	12.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.7	31.1
0°-40°	1008.4	50.6
0°-60°	1711.9	85.9
0°-90°	1993.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1993.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	803	
5°	801	76
15°	770	217
25°	711	327
35°	622	389
45°	504	388
55°	353	316
65°	195	194
75°	68	75
85°	9	12
90°	0	



TEST NUMBER: P204689

CATALOG NUMBER: LD6B20D010 EU6B10209050 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	803.1
2.5°	804.3
5°	800.7
7.5°	796.0
10°	790.1
12.5°	779.5
15°	770.0
17.5°	755.9
20°	740.5
22.5°	726.3
25°	711.0
27.5°	689.7
30°	668.5
32.5°	648.4
35°	622.4
37.5°	594.1
40°	568.1
42.5°	536.2
45°	504.3
47.5°	470.1
50°	433.4
52.5°	395.7
55°	353.1
57.5°	311.8
60°	271.6
62.5°	232.7
65°	194.9
67.5°	159.4
70°	126.4
72.5°	95.7
75°	68.5
77.5°	44.9
80°	27.2
82.5°	16.5
85°	9.4
87.5°	4.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)