

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204976

Luminaire Tested: **LD6B15D010 EU6B10208027 6LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10208027 6LBCSMMS1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1442.9 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204976

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P204976

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204976

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	4.3
10°-20°	175.2	12.1
20°-30°	255.9	17.7
30°-40°	292.7	20.3
40°-50°	281.3	19.5
50°-60°	217.2	15.1
60°-70°	121.2	8.4
70°-80°	35.3	2.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	493.6	34.2
0°-40°	786.3	54.5
0°-60°	1284.8	89.0
0°-90°	1442.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1442.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	663	
5°	657	62
15°	622	175
25°	556	256
35°	468	293
45°	367	281
55°	244	217
65°	121	121
75°	31	35
85°	1	2
90°	0	



TEST NUMBER: P204976

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	662.6
2.5°	662.6
5°	657.0
7.5°	654.2
10°	644.9
12.5°	633.7
15°	621.5
17.5°	609.4
20°	591.7
22.5°	577.7
25°	556.2
27.5°	534.7
30°	513.3
32.5°	491.8
35°	468.5
37.5°	445.1
40°	418.1
42.5°	393.8
45°	366.8
47.5°	336.0
50°	307.0
52.5°	275.3
55°	243.6
57.5°	210.9
60°	180.1
62.5°	149.3
65°	121.3
67.5°	95.2
70°	70.9
72.5°	49.5
75°	30.8
77.5°	15.9
80°	5.6
82.5°	1.9
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)