

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203840

Luminaire Tested: **LD6B15D010 EU6B10208027 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10208027 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 705.5 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203840

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203840

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203840

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.6	11.0
10°-20°	191.5	27.1
20°-30°	232.0	32.9
30°-40°	158.1	22.4
40°-50°	37.6	5.3
50°-60°	5.9	0.8
60°-70°	2.2	0.3
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.1	71.0
0°-40°	659.2	93.4
0°-60°	702.7	99.6
0°-90°	705.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	705.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	858	
5°	834	78
15°	686	191
25°	507	232
35°	253	158
45°	40	38
55°	6	6
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203840

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	857.6
2.5°	852.8
5°	833.5
7.5°	807.8
10°	770.8
12.5°	728.9
15°	685.5
17.5°	640.4
20°	595.4
22.5°	550.3
25°	506.9
27.5°	466.6
30°	408.7
32.5°	333.1
35°	252.6
37.5°	180.2
40°	119.1
42.5°	74.0
45°	40.2
47.5°	20.9
50°	11.3
52.5°	8.0
55°	6.4
57.5°	4.8
60°	3.2
62.5°	3.2
65°	1.6
67.5°	1.6
70°	1.6
72.5°	1.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)