

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204912

Luminaire Tested: **LD6B40D010 EU6B30508030 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204912
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508030 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3877.1 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204912

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204912

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88																
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75																
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65																
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56																
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49																
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43																
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39																
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35																
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31																
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204912

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.8	4.0
10°-20°	441.1	11.4
20°-30°	663.2	17.1
30°-40°	786.9	20.3
40°-50°	778.7	20.1
50°-60°	611.6	15.8
60°-70°	342.9	8.8
70°-80°	96.3	2.5
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1259.1	32.5
0°-40°	2046.0	52.8
0°-60°	3436.3	88.6
0°-90°	3877.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3877.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1637	
5°	1634	155
15°	1565	441
25°	1440	663
35°	1262	787
45°	1014	779
55°	689	612
65°	342	343
75°	83	96
85°	0	2
90°	0	



TEST NUMBER: P204912

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1637.1
2.5°	1631.6
5°	1634.3
7.5°	1620.4
10°	1603.8
12.5°	1584.3
15°	1564.8
17.5°	1539.8
20°	1506.5
22.5°	1473.1
25°	1439.8
27.5°	1403.6
30°	1356.4
32.5°	1309.1
35°	1261.9
37.5°	1206.3
40°	1142.4
42.5°	1081.2
45°	1014.5
47.5°	939.5
50°	861.6
52.5°	772.7
55°	689.3
57.5°	594.8
60°	505.9
62.5°	425.3
65°	341.9
67.5°	269.6
70°	200.1
72.5°	136.2
75°	83.4
77.5°	41.7
80°	11.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)