

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203571

Luminaire Tested: **LD6B40D010 EU6B30508030 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508030 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3350.4 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203571

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203571

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203571

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.9	6.9
10°-20°	618.6	18.5
20°-30°	830.6	24.8
30°-40°	681.3	20.3
40°-50°	409.2	12.2
50°-60°	271.9	8.1
60°-70°	182.2	5.4
70°-80°	98.1	2.9
80°-90°	27.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1680.1	50.1
0°-40°	2361.4	70.5
0°-60°	3042.4	90.8
0°-90°	3350.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3350.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2500	
5°	2458	231
15°	2204	619
25°	1830	831
35°	1081	681
45°	518	409
55°	300	272
65°	185	182
75°	92	98
85°	23	28
90°	0	



TEST NUMBER: P203571

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2500.0
2.5°	2481.5
5°	2458.4
7.5°	2407.5
10°	2347.5
12.5°	2273.5
15°	2204.2
17.5°	2121.0
20°	2037.9
22.5°	1945.4
25°	1829.9
27.5°	1691.3
30°	1506.4
32.5°	1298.5
35°	1081.3
37.5°	896.5
40°	739.4
42.5°	614.6
45°	517.6
47.5°	439.0
50°	383.5
52.5°	337.3
55°	300.4
57.5°	268.0
60°	240.3
62.5°	207.9
65°	184.8
67.5°	157.1
70°	134.0
72.5°	110.9
75°	92.4
77.5°	73.9
80°	55.5
82.5°	41.6
85°	23.1
87.5°	9.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)