

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204464

Luminaire Tested: **LD6B15D010 EU6B10209027 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10209027 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1102.6 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204464

CATALOG NUMBER: LD6B15D010 EU6B10209027 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204464

CATALOG NUMBER: LD6B15D010 EU6B10209027 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204464

CATALOG NUMBER: LD6B15D010 EU6B10209027 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.9	4.2
10°-20°	130.3	11.8
20°-30°	193.8	17.6
30°-40°	225.5	20.4
40°-50°	219.8	19.9
50°-60°	169.0	15.3
60°-70°	93.4	8.5
70°-80°	24.7	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.9	33.6
0°-40°	595.4	54.0
0°-60°	984.2	89.3
0°-90°	1102.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1102.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	486	
5°	484	46
15°	461	130
25°	421	194
35°	362	225
45°	285	220
55°	189	169
65°	94	93
75°	21	25
85°	0	0
90°	0	



TEST NUMBER: P204464

CATALOG NUMBER: LD6B15D010 EU6B10209027 6LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	486.4
2.5°	486.4
5°	483.6
7.5°	479.4
10°	476.6
12.5°	468.2
15°	461.2
17.5°	454.3
20°	444.5
22.5°	434.7
25°	420.7
27.5°	406.7
30°	392.8
32.5°	377.4
35°	362.0
37.5°	342.4
40°	325.7
42.5°	307.5
45°	285.1
47.5°	264.2
50°	240.4
52.5°	215.2
55°	188.7
57.5°	163.5
60°	139.8
62.5°	116.0
65°	93.6
67.5°	72.7
70°	53.1
72.5°	36.3
75°	21.0
77.5°	9.8
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)