

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204918

Luminaire Tested: **LD6B40D010 EU6B30509030 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30509030 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3311.1 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204918

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204918

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88																			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75																			
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56																			
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39																			
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35																			
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31																			
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204918

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.2	4.0
10°-20°	376.7	11.4
20°-30°	566.4	17.1
30°-40°	672.0	20.3
40°-50°	665.0	20.1
50°-60°	522.4	15.8
60°-70°	292.9	8.8
70°-80°	82.2	2.5
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.3	32.5
0°-40°	1747.3	52.8
0°-60°	2934.7	88.6
0°-90°	3311.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3311.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1398	
5°	1396	132
15°	1336	377
25°	1230	566
35°	1078	672
45°	866	665
55°	589	522
65°	292	293
75°	71	82
85°	0	1
90°	0	



TEST NUMBER: P204918

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1398.1
2.5°	1393.4
5°	1395.8
7.5°	1383.9
10°	1369.6
12.5°	1353.0
15°	1336.4
17.5°	1315.0
20°	1286.6
22.5°	1258.1
25°	1229.6
27.5°	1198.7
30°	1158.4
32.5°	1118.0
35°	1077.7
37.5°	1030.2
40°	975.6
42.5°	923.4
45°	866.4
47.5°	802.3
50°	735.9
52.5°	659.9
55°	588.7
57.5°	508.0
60°	432.0
62.5°	363.2
65°	292.0
67.5°	230.3
70°	170.9
72.5°	116.3
75°	71.2
77.5°	35.6
80°	9.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)