

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203841

Luminaire Tested: **LD6B15D010 EU6B10208030 6LBNGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203841  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B15D010 EU6B10208030 6LBNGPH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 737.4 lumens  
Efficiency: N/A  
Efficacy: 51.6 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203841

CATALOG NUMBER: LD6B15D010 EU6B10208030 6LBNGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203841

CATALOG NUMBER: LD6B15D010 EU6B10208030 6LBNGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	79	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203841

CATALOG NUMBER: LD6B15D010 EU6B10208030 6LBNGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.1	11.0
10°-20°	200.1	27.1
20°-30°	242.5	32.9
30°-40°	165.2	22.4
40°-50°	39.4	5.3
50°-60°	6.1	0.8
60°-70°	2.3	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	523.7	71.0
0°-40°	688.9	93.4
0°-60°	734.4	99.6
0°-90°	737.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	737.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	896	
5°	871	81
15°	716	200
25°	530	242
35°	264	165
45°	42	39
55°	7	6
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203841

CATALOG NUMBER: LD6B15D010 EU6B10208030 6LBNGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	896.3
2.5°	891.2
5°	871.1
7.5°	844.1
10°	805.5
12.5°	761.8
15°	716.3
17.5°	669.3
20°	622.2
22.5°	575.1
25°	529.7
27.5°	487.7
30°	427.1
32.5°	348.1
35°	264.0
37.5°	188.3
40°	124.4
42.5°	77.4
45°	42.0
47.5°	21.9
50°	11.8
52.5°	8.4
55°	6.7
57.5°	5.0
60°	3.4
62.5°	3.4
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)