

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204092

Luminaire Tested: **LD6B40D010 EU6B30509030 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30509030 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2575.2 lumens
Efficiency: N/A
Efficacy: 61.6 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204092

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204092

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204092

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.1	7.6
10°-20°	519.8	20.2
20°-30°	694.0	26.9
30°-40°	559.9	21.7
40°-50°	268.3	10.4
50°-60°	159.1	6.2
60°-70°	105.7	4.1
70°-80°	56.6	2.2
80°-90°	15.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1409.9	54.8
0°-40°	1969.9	76.5
0°-60°	2397.2	93.1
0°-90°	2575.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2575.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2112	
5°	2087	196
15°	1850	520
25°	1518	694
35°	896	560
45°	332	268
55°	176	159
65°	106	106
75°	53	57
85°	12	16
90°	0	



TEST NUMBER: P204092

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2111.9
2.5°	2111.9
5°	2087.4
7.5°	2046.5
10°	1989.2
12.5°	1927.8
15°	1850.0
17.5°	1776.3
20°	1694.5
22.5°	1608.5
25°	1518.5
27.5°	1424.3
30°	1289.3
32.5°	1101.0
35°	896.3
37.5°	708.1
40°	548.5
42.5°	425.7
45°	331.5
47.5°	261.9
50°	221.0
52.5°	196.5
55°	176.0
57.5°	159.6
60°	139.2
62.5°	122.8
65°	106.4
67.5°	90.0
70°	77.8
72.5°	65.5
75°	53.2
77.5°	40.9
80°	32.7
82.5°	24.6
85°	12.3
87.5°	4.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)