

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204190

Luminaire Tested: **LD6B40D010 EU6B30508035 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204190
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508035 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4458.6 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204190

CATALOG NUMBER: LD6B40D010 EU6B30508035 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204190

CATALOG NUMBER: LD6B40D010 EU6B30508035 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204190

CATALOG NUMBER: LD6B40D010 EU6B30508035 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.4	4.9
10°-20°	593.6	13.3
20°-30°	824.4	18.5
30°-40°	899.7	20.2
40°-50°	839.2	18.8
50°-60°	637.0	14.3
60°-70°	348.8	7.8
70°-80°	96.0	2.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1636.5	36.7
0°-40°	2536.2	56.9
0°-60°	4012.4	90.0
0°-90°	4458.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4458.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2332	
5°	2312	218
15°	2116	594
25°	1792	824
35°	1438	900
45°	1090	839
55°	712	637
65°	348	349
75°	84	96
85°	0	1
90°	0	



TEST NUMBER: P204190

CATALOG NUMBER: LD6B40D010 EU6B30508035 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2331.8
2.5°	2331.8
5°	2312.2
7.5°	2282.7
10°	2238.5
12.5°	2179.6
15°	2115.8
17.5°	2037.3
20°	1963.6
22.5°	1875.3
25°	1791.8
27.5°	1708.4
30°	1615.1
32.5°	1526.7
35°	1438.4
37.5°	1350.0
40°	1266.5
42.5°	1178.2
45°	1089.8
47.5°	1001.4
50°	903.3
52.5°	810.0
55°	711.8
57.5°	618.5
60°	525.3
62.5°	432.0
65°	348.5
67.5°	270.0
70°	201.3
72.5°	137.5
75°	83.5
77.5°	39.3
80°	9.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)