

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205485

Luminaire Tested: **LD6B15D010 EU6B10208035 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10208035 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 838.5 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205485

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205485

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205485

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.3	9.6
10°-20°	208.3	24.8
20°-30°	265.4	31.6
30°-40°	187.5	22.4
40°-50°	68.5	8.2
50°-60°	19.0	2.3
60°-70°	6.9	0.8
70°-80°	2.5	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.9	66.1
0°-40°	741.5	88.4
0°-60°	828.9	98.9
0°-90°	838.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	838.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	874	
5°	858	80
15°	742	208
25°	589	265
35°	298	188
45°	83	68
55°	20	19
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P205485

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	873.8
2.5°	870.4
5°	858.5
7.5°	834.8
10°	809.4
12.5°	775.6
15°	741.7
17.5°	707.8
20°	674.0
22.5°	633.3
25°	589.3
27.5°	528.3
30°	460.6
32.5°	379.3
35°	298.0
37.5°	226.9
40°	165.9
42.5°	120.2
45°	83.0
47.5°	55.9
50°	37.3
52.5°	25.4
55°	20.3
57.5°	15.2
60°	11.9
62.5°	8.5
65°	6.8
67.5°	5.1
70°	3.4
72.5°	3.4
75°	1.7
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)