

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35093

Luminaire Tested: **LD6B15D010 EU6B10208035 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35093
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10208035 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1178.9 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Ellipsoidal Spheroid (W: 0.46' x L: 0.46' x H: 1')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35093

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P35093

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69			
6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56			
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P35093

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	10.2
10°-20°	308.9	26.2
20°-30°	379.4	32.2
30°-40°	260.1	22.1
40°-50°	83.6	7.1
50°-60°	16.9	1.4
60°-70°	6.7	0.6
70°-80°	2.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.6	68.6
0°-40°	1068.7	90.7
0°-60°	1169.3	99.2
0°-90°	1178.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1178.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1311	
5°	1286	120
15°	1105	309
25°	837	379
35°	415	260
45°	99	84
55°	17	17
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P35093

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1311
2.5°	1303
5°	1286
7.5°	1254
10°	1211
12.5°	1158
15°	1105
17.5°	1046
20°	981
22.5°	913
25°	837
27.5°	753
30°	647
32.5°	530
35°	415
37.5°	310
40°	223
42.5°	152
45°	99
47.5°	61
50°	37
52.5°	23
55°	17
57.5°	13
60°	10
62.5°	8
65°	7
67.5°	5
70°	4
72.5°	3
75°	2
77.5°	2
80°	1
82.5°	1
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)