

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205382

Luminaire Tested: **LD6B15D010 EU6B10208035 6LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205382  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B15D010 EU6B10208035 6LBSLI1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1620.2 lumens  
Efficiency: N/A  
Efficacy: 113.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205382

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205382

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68				68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60				60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53				53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47				47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43				43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39				39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36				36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33				33

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205382

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.2	5.8
10°-20°	239.9	14.8
20°-30°	305.9	18.9
30°-40°	317.2	19.6
40°-50°	292.3	18.0
50°-60°	219.8	13.6
60°-70°	118.7	7.3
70°-80°	31.8	2.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	639.9	39.5
0°-40°	957.1	59.1
0°-60°	1469.2	90.7
0°-90°	1620.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1620.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1022	
5°	1007	94
15°	856	240
25°	664	306
35°	506	317
45°	380	292
55°	246	220
65°	119	119
75°	28	32
85°	0	0
90°	0	



TEST NUMBER: P205382

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBSL11

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1022.4
2.5°	1019.0
5°	1006.9
7.5°	984.6
10°	945.0
12.5°	905.4
15°	855.5
17.5°	809.0
20°	760.8
22.5°	710.9
25°	664.4
27.5°	619.7
30°	578.3
32.5°	540.5
35°	506.1
37.5°	473.3
40°	442.4
42.5°	409.7
45°	380.4
47.5°	347.7
50°	315.0
52.5°	280.6
55°	246.1
57.5°	211.7
60°	179.0
62.5°	148.0
65°	118.8
67.5°	91.2
70°	67.1
72.5°	46.5
75°	27.5
77.5°	12.0
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)