

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203024

Luminaire Tested: **LD6B15D010 EU6B10209035 6LBWB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203024  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B15D010 EU6B10209035 6LBWB1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 714.5 lumens  
Efficiency: N/A  
Efficacy: 50.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203024

CATALOG NUMBER: LD6B15D010 EU6B10209035 6LBWB1

### Luminous Intensity Polar Plot





TEST NUMBER: P203024

CATALOG NUMBER: LD6B15D010 EU6B10209035 6LBWB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	56	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46	46	46	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203024

CATALOG NUMBER: LD6B15D010 EU6B10209035 6LBWB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.6	7.1
10°-20°	141.6	19.8
20°-30°	198.3	27.8
30°-40°	189.4	26.5
40°-50°	107.9	15.1
50°-60°	26.3	3.7
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	390.5	54.7
0°-40°	579.9	81.2
0°-60°	714.1	100.0
0°-90°	714.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	714.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	538	
5°	534	51
15°	502	142
25°	434	198
35°	308	189
45°	138	108
55°	26	26
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203024

CATALOG NUMBER: LD6B15D010 EU6B10209035 6LBWB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	538.5
2.5°	538.5
5°	534.1
7.5°	528.3
10°	523.9
12.5°	515.2
15°	502.1
17.5°	490.4
20°	475.9
22.5°	457.0
25°	433.7
27.5°	407.5
30°	378.4
32.5°	343.5
35°	308.5
37.5°	266.3
40°	221.2
42.5°	179.0
45°	138.3
47.5°	101.9
50°	71.3
52.5°	45.1
55°	26.2
57.5°	11.6
60°	2.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)