

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202813

Luminaire Tested: **LD6B15D010 EU6B10208040 6LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202813  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B15D010 EU6B10208040 6LBWWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1388.6 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202813

CATALOG NUMBER: LD6B15D010 EU6B10208040 6LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202813

CATALOG NUMBER: LD6B15D010 EU6B10208040 6LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202813

CATALOG NUMBER: LD6B15D010 EU6B10208040 6LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.9	6.0
10°-20°	246.5	17.8
20°-30°	371.1	26.7
30°-40°	379.4	27.3
40°-50°	230.4	16.6
50°-60°	64.9	4.7
60°-70°	9.9	0.7
70°-80°	3.2	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.5	50.4
0°-40°	1080.0	77.8
0°-60°	1375.3	99.0
0°-90°	1388.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1388.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	862	
5°	866	83
15°	873	247
25°	810	371
35°	615	379
45°	296	230
55°	64	65
65°	9	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P202813

CATALOG NUMBER: LD6B15D010 EU6B10208040 6LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	862.5
2.5°	862.5
5°	866.0
7.5°	871.2
10°	871.2
12.5°	874.7
15°	872.9
17.5°	869.5
20°	857.3
22.5°	839.8
25°	810.2
27.5°	777.1
30°	731.8
32.5°	677.8
35°	615.1
37.5°	545.4
40°	465.2
42.5°	381.6
45°	296.2
47.5°	219.5
50°	155.1
52.5°	104.5
55°	64.5
57.5°	38.3
60°	19.2
62.5°	12.2
65°	8.7
67.5°	7.0
70°	5.2
72.5°	3.5
75°	3.5
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)