

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204312

Luminaire Tested: **LD6B50D010TE EU6B30509035 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204312
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509035 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4848.6 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204312

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204312

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				89
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77				77
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67				67
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59				59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204312

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.7	5.5
10°-20°	690.3	14.2
20°-30°	902.9	18.6
30°-40°	956.1	19.7
40°-50°	891.8	18.4
50°-60°	675.4	13.9
60°-70°	365.8	7.5
70°-80°	98.1	2.0
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1859.9	38.4
0°-40°	2816.1	58.1
0°-60°	4383.2	90.4
0°-90°	4848.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4848.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2892	
5°	2849	267
15°	2467	690
25°	1963	903
35°	1528	956
45°	1162	892
55°	759	675
65°	366	366
75°	85	98
85°	0	1
90°	0	



TEST NUMBER: P204312

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2891.7
2.5°	2881.0
5°	2849.2
7.5°	2780.2
10°	2690.0
12.5°	2583.9
15°	2467.2
17.5°	2334.5
20°	2217.8
22.5°	2085.2
25°	1963.1
27.5°	1841.1
30°	1724.4
32.5°	1623.6
35°	1528.1
37.5°	1432.6
40°	1342.4
42.5°	1252.2
45°	1162.0
47.5°	1061.2
50°	960.3
52.5°	859.5
55°	758.7
57.5°	652.6
60°	551.8
62.5°	456.3
65°	366.1
67.5°	281.2
70°	206.9
72.5°	143.3
75°	84.9
77.5°	37.1
80°	10.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)