

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202870

Luminaire Tested: **LD6B50D010TE EU6B30509035 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509035 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4233.2 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202870

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202870

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202870

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.7	6.0
10°-20°	751.5	17.8
20°-30°	1131.3	26.7
30°-40°	1156.7	27.3
40°-50°	702.5	16.6
50°-60°	197.8	4.7
60°-70°	30.1	0.7
70°-80°	9.8	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2135.6	50.4
0°-40°	3292.3	77.8
0°-60°	4192.6	99.0
0°-90°	4233.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4233.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2629	
5°	2640	253
15°	2661	752
25°	2470	1131
35°	1875	1157
45°	903	703
55°	196	198
65°	27	30
75°	11	10
85°	0	1
90°	0	



TEST NUMBER: P202870

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2629.3
2.5°	2629.3
5°	2639.9
7.5°	2655.9
10°	2655.9
12.5°	2666.5
15°	2661.2
17.5°	2650.5
20°	2613.4
22.5°	2560.2
25°	2469.9
27.5°	2369.0
30°	2230.9
32.5°	2066.3
35°	1875.0
37.5°	1662.6
40°	1418.2
42.5°	1163.3
45°	903.0
47.5°	669.3
50°	472.7
52.5°	318.7
55°	196.5
57.5°	116.9
60°	58.4
62.5°	37.2
65°	26.6
67.5°	21.2
70°	15.9
72.5°	10.6
75°	10.6
77.5°	5.3
80°	5.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)