

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202819

Luminaire Tested: **LD6B15D010 EU6B10209040 6LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202819  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B15D010 EU6B10209040 6LBWWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1163.4 lumens  
Efficiency: N/A  
Efficacy: 81.4 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202819

CATALOG NUMBER: LD6B15D010 EU6B10209040 6LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202819

CATALOG NUMBER: LD6B15D010 EU6B10209040 6LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62																			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56																			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202819

CATALOG NUMBER: LD6B15D010 EU6B10209040 6LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.5	6.0
10°-20°	206.5	17.8
20°-30°	310.9	26.7
30°-40°	317.9	27.3
40°-50°	193.1	16.6
50°-60°	54.4	4.7
60°-70°	8.3	0.7
70°-80°	2.7	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	586.9	50.4
0°-40°	904.8	77.8
0°-60°	1152.2	99.0
0°-90°	1163.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1163.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	723	
5°	726	69
15°	731	207
25°	679	311
35°	515	318
45°	248	193
55°	54	54
65°	7	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P202819

CATALOG NUMBER: LD6B15D010 EU6B10209040 6LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	722.6
2.5°	722.6
5°	725.5
7.5°	729.9
10°	729.9
12.5°	732.8
15°	731.4
17.5°	728.4
20°	718.2
22.5°	703.6
25°	678.8
27.5°	651.1
30°	613.1
32.5°	567.9
35°	515.3
37.5°	456.9
40°	389.8
42.5°	319.7
45°	248.2
47.5°	183.9
50°	129.9
52.5°	87.6
55°	54.0
57.5°	32.1
60°	16.1
62.5°	10.2
65°	7.3
67.5°	5.8
70°	4.4
72.5°	2.9
75°	2.9
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)