

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204050

Luminaire Tested: **LD6B15D010 EU6B10208050 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10208050 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1095.7 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204050

CATALOG NUMBER: LD6B15D010 EU6B10208050 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204050

CATALOG NUMBER: LD6B15D010 EU6B10208050 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204050

CATALOG NUMBER: LD6B15D010 EU6B10208050 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	7.6
10°-20°	221.2	20.2
20°-30°	295.3	27.0
30°-40°	238.2	21.7
40°-50°	114.2	10.4
50°-60°	67.7	6.2
60°-70°	45.0	4.1
70°-80°	24.1	2.2
80°-90°	6.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.9	54.8
0°-40°	838.1	76.5
0°-60°	1020.0	93.1
0°-90°	1095.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1095.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	899	
5°	888	83
15°	787	221
25°	646	295
35°	381	238
45°	141	114
55°	75	68
65°	45	45
75°	23	24
85°	5	7
90°	0	



TEST NUMBER: P204050

CATALOG NUMBER: LD6B15D010 EU6B10208050 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	898.6
2.5°	898.6
5°	888.1
7.5°	870.7
10°	846.3
12.5°	820.2
15°	787.1
17.5°	755.8
20°	721.0
22.5°	684.4
25°	646.1
27.5°	606.0
30°	548.6
32.5°	468.5
35°	381.4
37.5°	301.3
40°	233.4
42.5°	181.1
45°	141.1
47.5°	111.5
50°	94.0
52.5°	83.6
55°	74.9
57.5°	67.9
60°	59.2
62.5°	52.2
65°	45.3
67.5°	38.3
70°	33.1
72.5°	27.9
75°	22.6
77.5°	17.4
80°	13.9
82.5°	10.4
85°	5.2
87.5°	1.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)