

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203648

Luminaire Tested: **LD6B20D010 EU6B10208030 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208030 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1281.9 lumens
Efficiency: N/A
Efficacy: 61.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203648

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203648

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203648

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	11.5
10°-20°	352.4	27.5
20°-30°	403.7	31.5
30°-40°	271.3	21.2
40°-50°	77.5	6.0
50°-60°	19.0	1.5
60°-70°	7.2	0.6
70°-80°	2.7	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	903.9	70.5
0°-40°	1175.2	91.7
0°-60°	1271.6	99.2
0°-90°	1281.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1281.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1643	
5°	1596	148
15°	1265	352
25°	881	404
35°	432	271
45°	89	78
55°	21	19
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P203648

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1643.3
2.5°	1631.6
5°	1596.5
7.5°	1533.4
10°	1456.3
12.5°	1358.1
15°	1264.6
17.5°	1166.4
20°	1068.3
22.5°	974.8
25°	881.3
27.5°	794.8
30°	694.2
32.5°	561.0
35°	432.4
37.5°	315.6
40°	217.4
42.5°	142.6
45°	88.8
47.5°	53.8
50°	32.7
52.5°	25.7
55°	21.0
57.5°	16.4
60°	11.7
62.5°	9.4
65°	7.0
67.5°	4.7
70°	4.7
72.5°	2.3
75°	2.3
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)