

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204060

Luminaire Tested: **LD6B20D010 EU6B10208030 6LBNMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204060  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B20D010 EU6B10208030 6LBNMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1471.0 lumens  
Efficiency: N/A  
Efficacy: 70.7 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204060

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBNMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204060

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBNMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204060

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBNMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.0	7.6
10°-20°	296.9	20.2
20°-30°	396.4	26.9
30°-40°	319.8	21.7
40°-50°	153.3	10.4
50°-60°	90.9	6.2
60°-70°	60.4	4.1
70°-80°	32.4	2.2
80°-90°	8.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	805.4	54.8
0°-40°	1125.2	76.5
0°-60°	1369.4	93.1
0°-90°	1471.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1471.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1206	
5°	1192	112
15°	1057	297
25°	867	396
35°	512	320
45°	189	153
55°	100	91
65°	61	60
75°	30	32
85°	7	9
90°	0	



TEST NUMBER: P204060

CATALOG NUMBER: LD6B20D010 EU6B10208030 6LBNMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1206.4
2.5°	1206.4
5°	1192.4
7.5°	1169.0
10°	1136.3
12.5°	1101.2
15°	1056.8
17.5°	1014.7
20°	967.9
22.5°	918.8
25°	867.4
27.5°	813.6
30°	736.5
32.5°	628.9
35°	512.0
37.5°	404.5
40°	313.3
42.5°	243.2
45°	189.4
47.5°	149.6
50°	126.3
52.5°	112.2
55°	100.5
57.5°	91.2
60°	79.5
62.5°	70.1
65°	60.8
67.5°	51.4
70°	44.4
72.5°	37.4
75°	30.4
77.5°	23.4
80°	18.7
82.5°	14.0
85°	7.0
87.5°	2.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)