

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205246

Luminaire Tested: **LD6B60D010TE EU6B60709024 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205246
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709024 6LBWL11
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4360.7 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205246

CATALOG NUMBER: LD6B60D010TE EU6B60709024 6LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205246

CATALOG NUMBER: LD6B60D010TE EU6B60709024 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	97	91	86	81	88	84	80		86	82	79		83
4	93	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	78	71	66	86	77	71	66	75	70	65		73	69	65		72
6	82	72	65	60	81	71	65	60	70	64	59		68	63	59		67
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58
9	69	57	51	46	67	57	50	46	56	50	46		55	50	46		54
10	65	54	47	43	64	53	47	43	52	46	42		51	46	42		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205246

CATALOG NUMBER: LD6B60D010TE EU6B60709024 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.8	6.0
10°-20°	789.9	18.1
20°-30°	1190.8	27.3
30°-40°	1218.8	27.9
40°-50°	710.1	16.3
50°-60°	163.2	3.7
60°-70°	20.0	0.5
70°-80°	5.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2243.5	51.4
0°-40°	3462.3	79.4
0°-60°	4335.5	99.4
0°-90°	4360.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4360.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2724	
5°	2739	263
15°	2798	790
25°	2610	1191
35°	1978	1219
45°	915	710
55°	158	163
65°	15	20
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P205246

CATALOG NUMBER: LD6B60D010TE EU6B60709024 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2724.2
2.5°	2719.3
5°	2739.1
7.5°	2758.9
10°	2783.6
12.5°	2788.5
15°	2798.4
17.5°	2788.5
20°	2763.8
22.5°	2684.7
25°	2610.5
27.5°	2491.9
30°	2338.6
32.5°	2180.4
35°	1977.7
37.5°	1750.2
40°	1498.1
42.5°	1216.3
45°	914.7
47.5°	637.8
50°	420.3
52.5°	267.0
55°	158.2
57.5°	84.1
60°	44.5
62.5°	24.7
65°	14.8
67.5°	14.8
70°	9.9
72.5°	4.9
75°	4.9
77.5°	4.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)