

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204691

Luminaire Tested: **LD6B20D010 EU6B10209730 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209730 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1707.4 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204691

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204691

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																	
	1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86	86	86	86	86	86	86	86	86	86	86	86																
	2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74	74	74	74	74	74	74	74	74	74	74	74																
	3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63	63	63	63	63	63	63	63	63	63	63	63																
	4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54	54	54	54	54	54	54	54	54	54	54	54																
	5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47	47	47	47	47	47	47	47	47	47	47	47																
	6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42	42	42	42	42	42	42	42	42	42	42	42																
	7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37	37	37	37	37	37	37	37	37	37	37	37																
	8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33	33	33	33	33	33	33	33	33	33	33	33																
	9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30	30	30	30	30	30	30	30	30	30	30	30																
	10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27	27	27	27	27	27	27	27	27	27	27	27																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204691

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.2	3.8
10°-20°	185.8	10.9
20°-30°	279.8	16.4
30°-40°	333.0	19.5
40°-50°	332.4	19.5
50°-60°	270.3	15.8
60°-70°	166.3	9.7
70°-80°	64.4	3.8
80°-90°	10.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.8	31.1
0°-40°	863.8	50.6
0°-60°	1466.4	85.9
0°-90°	1707.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1707.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	688	
5°	686	65
15°	660	186
25°	609	280
35°	533	333
45°	432	332
55°	302	270
65°	167	166
75°	59	64
85°	8	10
90°	0	



TEST NUMBER: P204691

CATALOG NUMBER: LD6B20D010 EU6B10209730 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	687.9
2.5°	688.9
5°	685.9
7.5°	681.8
10°	676.8
12.5°	667.7
15°	659.6
17.5°	647.5
20°	634.3
22.5°	622.2
25°	609.0
27.5°	590.8
30°	572.6
32.5°	555.4
35°	533.1
37.5°	508.9
40°	486.6
42.5°	459.3
45°	432.0
47.5°	402.6
50°	371.3
52.5°	338.9
55°	302.5
57.5°	267.1
60°	232.7
62.5°	199.3
65°	166.9
67.5°	136.6
70°	108.2
72.5°	81.9
75°	58.7
77.5°	38.4
80°	23.3
82.5°	14.2
85°	8.1
87.5°	4.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)