

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203546

Luminaire Tested: **LD6B20D010 EU6B10208035 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208035 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1675.0 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203546

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203546

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89				89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79				79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71				71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64				64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58				58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53				53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48				48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44				44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41				41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38				38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203546

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.5	6.9
10°-20°	309.3	18.5
20°-30°	415.2	24.8
30°-40°	340.6	20.3
40°-50°	204.5	12.2
50°-60°	135.9	8.1
60°-70°	91.1	5.4
70°-80°	49.0	2.9
80°-90°	13.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	839.9	50.1
0°-40°	1180.6	70.5
0°-60°	1521.0	90.8
0°-90°	1675.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1675.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1250	
5°	1229	115
15°	1102	309
25°	915	415
35°	541	341
45°	259	205
55°	150	136
65°	92	91
75°	46	49
85°	12	14
90°	0	



TEST NUMBER: P203546

CATALOG NUMBER: LD6B20D010 EU6B10208035 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1249.8
2.5°	1240.6
5°	1229.0
7.5°	1203.6
10°	1173.6
12.5°	1136.6
15°	1102.0
17.5°	1060.4
20°	1018.8
22.5°	972.6
25°	914.8
27.5°	845.5
30°	753.1
32.5°	649.2
35°	540.6
37.5°	448.2
40°	369.6
42.5°	307.3
45°	258.7
47.5°	219.5
50°	191.7
52.5°	168.6
55°	150.2
57.5°	134.0
60°	120.1
62.5°	104.0
65°	92.4
67.5°	78.5
70°	67.0
72.5°	55.4
75°	46.2
77.5°	37.0
80°	27.7
82.5°	20.8
85°	11.6
87.5°	4.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)